



Main

| | |
|------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Range | PrismaSeT |
| Range of product | PrismaSeT P |
| Product or component type | Front plate |
| Accessory / separate part category | Installation accessory |
| Range compatibility | PrismaSeT PrismaSeT P cubicle |
| Type of front plate | Cut-out |
| Installed device | ComPact: fixed NS630b...1000 - control: toggle - horizontal installation ComPact: fixed NS630b...1000 - control: direct front rotary handle - horizontal installation |
| Poles description | 1 x 3P: mounting plate support: NS630b...1000 horizontal installation 1 x 4P: mounting plate support: NS630b...1000 horizontal installation |
| Operating position | Horizontal |

Complementary

| | |
|------------------------------------|-----------------------------------------------------------------------------------|
| Enclosure/cubicle description | Cubicle - width 650 mm depth 800 mm Cubicle + duct - width 650 mm depth 400 mm |
| Connection position | Front connection Rear connection |
| Number of vertical modules [50 mm] | 7 |
| Standards | IEC 61439-1 IEC 61439-2 |
| Product certifications | ASTA |
| Material | Steel |
| Surface finish | Matt Textured |
| Protective treatment | Electrophoresis treatment and hot-polymerised polyester epoxy powder |
| Colour | White (RAL 9003) |
| Height | 350 mm |
| Width | 500 mm |
| Net weight | 1.78 kg |

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

| | |
|------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Quantity per set | Set of 1 |
| Functional unit | <p>650 mm 400 mm PrismaSeT P cubicle + duct ComPact NS630b...1000 fixed toggle horizontal 3P 1 front connection 7</p> <p>650 mm 400 mm PrismaSeT P cubicle + duct ComPact NS630b...1000 fixed toggle horizontal 3P 1 connection transfer assembly 8</p> <p>650 mm 400 mm PrismaSeT P cubicle + duct ComPact NS630b...1000 fixed direct front rotary handle horizontal 3P 1 front connection 7</p> <p>650 mm 400 mm PrismaSeT P cubicle + duct ComPact NS630b...1000 fixed direct front rotary handle horizontal 3P 1 connection transfer assembly 8</p> <p>650 mm 800 mm PrismaSeT P cubicle ComPact NS630b...1000 fixed toggle horizontal 3P 1 rear connection 7</p> <p>650 mm 800 mm PrismaSeT P cubicle ComPact NS630b...1000 fixed direct front rotary handle horizontal 3P 1 rear connection 7</p> <p>650 mm 400 mm PrismaSeT P cubicle + duct ComPact NS630b...1000 fixed toggle horizontal 4P 1 front connection 7</p> <p>650 mm 400 mm PrismaSeT P cubicle + duct ComPact NS630b...1000 fixed toggle horizontal 4P 1 connection transfer assembly 8</p> <p>650 mm 400 mm PrismaSeT P cubicle + duct ComPact NS630b...1000 fixed direct front rotary handle horizontal 4P 1 front connection 7</p> <p>650 mm 400 mm PrismaSeT P cubicle + duct ComPact NS630b...1000 fixed direct front rotary handle horizontal 4P 1 connection transfer assembly 8</p> <p>650 mm 800 mm PrismaSeT P cubicle ComPact NS630b...1000 fixed toggle horizontal 4P 1 rear connection 7</p> <p>650 mm 800 mm PrismaSeT P cubicle ComPact NS630b...1000 fixed direct front rotary handle horizontal 4P 1 rear connection 7</p> |

Packing Units

| | |
|------------------------------|-----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 5.000 cm |
| Package 1 Width | 35.000 cm |
| Package 1 Length | 50.000 cm |
| Package 1 Weight | 1.761 kg |
| Unit Type of Package 2 | S04 |
| Number of Units in Package 2 | 5 |
| Package 2 Height | 30.000 cm |
| Package 2 Width | 40.000 cm |
| Package 2 Length | 60.000 cm |
| Package 2 Weight | 9.731 kg |
| Unit Type of Package 3 | P06 |
| Number of Units in Package 3 | 20 |
| Package 3 Height | 72.000 cm |
| Package 3 Width | 60.000 cm |
| Package 3 Length | 80.000 cm |
| Package 3 Weight | 45.000 kg |

Offer Sustainability

| | |
|----------------------------|------------------------------------------------------------------------------------------------|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |