


LVS03699

Front plate, PrismaSeT P, for MTZ1 06 to MTZ1 16, 3P, Withdrawable device, 37M, W400mm



Main

Range	PrismaSeT
Range of product	PrismaSeT P
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT P cubicle
Type of front plate	Cut-out
Installed device	ComPact: drawout NS1250 - control: toggle - vertical installation ComPact: drawout NS1250 - control: direct front rotary handle - vertical installation ComPact: drawout NS1250 - control: motor mechanism - vertical installation ComPact: drawout NS1600 - control: toggle - vertical installation ComPact: drawout NS1600 - control: direct front rotary handle - vertical installation ComPact: drawout NS1600 - control: motor mechanism - vertical installation ComPact: drawout NS630b...1000 - control: toggle - vertical installation ComPact: drawout NS630b...1000 - control: direct front rotary handle - vertical installation ComPact: drawout NS630b...1000 - control: motor mechanism - vertical installation Masterpact: drawout NT06...10 - control: toggle - vertical installation Masterpact: drawout NT12 - control: toggle - vertical installation Masterpact: drawout NT16 - control: toggle - vertical installation
Poles description	1 x 3P: mounting plate support: NS1250 vertical installation 1 x 3P: mounting plate support: NS1600 vertical installation 1 x 3P: mounting plate support: NS630b...1000 vertical installation 1 x 3P: mounting plate support: NT06...10 vertical installation 1 x 3P: mounting plate support: NT12 vertical installation 1 x 3P: mounting plate support: NT16 vertical installation
Operating position	Horizontal

Complementary

Enclosure/cubicle description	Cubicle duct - width 400 mm depth 400 mm
Connection position	Direct connection Front connection
Number of vertical modules [50 mm]	10
Standards	IEC 61439-1 IEC 61439-2
Product certifications	ASTA
Material	Steel

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Surface finish	Matt Textured
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9003)
Height	554 mm
Width	321 mm
Net weight	2.04 kg
Quantity per set	Set of 1
Functional unit	400 mm 400 mm PrismaSeT P cubicle ComPact NS1250 drawout toggle vertical 3P 1 direct 36 400 mm 400 mm PrismaSeT P cubicle ComPact NS1250 drawout direct front rotary handle vertical 3P 1 direct 36 400 mm 400 mm PrismaSeT P cubicle ComPact NS1250 drawout motor mechanism vertical 3P 1 direct 36 400 mm 400 mm PrismaSeT P cubicle ComPact NS1600 drawout toggle vertical 3P 1 direct 36 400 mm 400 mm PrismaSeT P cubicle ComPact NS1600 drawout direct front rotary handle vertical 3P 1 direct 36 400 mm 400 mm PrismaSeT P cubicle ComPact NS1600 drawout motor mechanism vertical 3P 1 direct 36 400 mm 400 mm PrismaSeT P cubicle ComPact NS630b...1000 drawout toggle vertical 3P 1 direct 36 400 mm 400 mm PrismaSeT P cubicle ComPact NS630b...1000 drawout direct front rotary handle vertical 3P 1 direct 36 400 mm 400 mm PrismaSeT P cubicle ComPact NS630b...1000 drawout motor mechanism vertical 3P 1 direct 36 400 mm 400 mm PrismaSeT P cubicle Masterpact NT06...10 drawout toggle vertical 3P 1 front connection 36 400 mm 400 mm PrismaSeT P cubicle Masterpact NT12 drawout toggle vertical 3P 1 front connection 36 400 mm 400 mm PrismaSeT P cubicle Masterpact NT16 drawout toggle vertical 3P 1 front connection 36

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.300 cm
Package 1 Width	32.500 cm
Package 1 Length	56.600 cm
Package 1 Weight	1.973 kg
Unit Type of Package 2	S04
Number of Units in Package 2	5
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	10.795 kg
Unit Type of Package 3	P12
Number of Units in Package 3	20
Package 3 Height	44.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	54.500 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration

RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
