

# LVS03903

Mounting Plate, PrismaSeT p, for 96X96 Cut-Out for Metering Dev/P-Button for Front Plate 03904/VISOR 03928



## Main

Range	PrismaSeT
Range of product	PrismaSeT G PrismaSeT P
Product or component type	Mounting plate
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT G enclosure PrismaSeT PrismaSeT P cubicle
Installation description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Cubicle - width 400 mm depth 400 mm Cubicle - width 650 mm depth 400 mm Cubicle duct - width 300 mm depth 400 mm
Installed device	Human-switchboard interface: 96 x 96 mm device PowerLogic: PM400...800 Enerlin'X: FDM121
Number of vertical modules [50 mm]	3 module(s): 96 x 96 mm device in 600 mm Widefloor-standing enclosure 3 module(s): 96 x 96 mm device in 600 mm Widewall-mounted enclosure 3 module(s): 96 x 96 mm device in 650 mm Widecubicle 3 module(s): 96 x 96 mm device in 300 mm Widecubicle duct 3 module(s): 96 x 96 mm device in 400 mm Widecubicle 3 module(s): FDM121 in 600 mm Widefloor-standing enclosure 3 module(s): FDM121 in 600 mm Widewall-mounted enclosure 3 module(s): FDM121 in 650 mm Widecubicle 3 module(s): FDM121 in 300 mm Widecubicle duct 3 module(s): FDM121 in 400 mm Widecubicle 3 module(s): PM400...800 in 600 mm Widefloor-standing enclosure 3 module(s): PM400...800 in 600 mm Widewall-mounted enclosure 3 module(s): PM400...800 in 650 mm Widecubicle 3 module(s): PM400...800 in 300 mm Widecubicle duct 3 module(s): PM400...800 in 400 mm Widecubicle
Standards	IEC 61439-2
Product certifications	ASTA

## Complementary

Material	Plastic
Colour	White (RAL 9001)
Width	101 mm
Height	150 mm
Depth	15 mm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Net weight	0.04 kg
Functional unit	600 mm PrismaSeT G floor-standing enclosure human-switchboard interface 96 x 96 mm device 4 3 600 mm PrismaSeT G wall-mounted enclosure human-switchboard interface 96 x 96 mm device 4 3 650 mm 400 mm PrismaSeT P cubicle human-switchboard interface 96 x 96 mm device 4 3 300 mm 400 mm PrismaSeT P cubicle duct human-switchboard interface 96 x 96 mm device 4 3 400 mm 400 mm PrismaSeT P cubicle human-switchboard interface 96 x 96 mm device 4 3 600 mm PrismaSeT G floor-standing enclosure PowerLogic 4 3 600 mm PrismaSeT G wall-mounted enclosure PowerLogic 4 3 650 mm 400 mm PrismaSeT P cubicle PowerLogic 4 3 300 mm 400 mm PrismaSeT P cubicle duct PowerLogic 4 3 400 mm 400 mm PrismaSeT P cubicle PowerLogic 4 3 600 mm PrismaSeT G floor-standing enclosure Enerlin'X FDM121 4 3 600 mm PrismaSeT G wall-mounted enclosure Enerlin'X FDM121 4 3 650 mm 400 mm PrismaSeT P cubicle Enerlin'X FDM121 4 3 300 mm 400 mm PrismaSeT P cubicle duct Enerlin'X FDM121 4 3 400 mm 400 mm PrismaSeT P cubicle Enerlin'X FDM121 4 3

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.5 cm
Package 1 Width	10.2 cm
Package 1 Length	15.0 cm
Package 1 Weight	32.0 g
Unit Type of Package 2	S04
Number of Units in Package 2	200
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	7.163 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
PVC free	Yes