



Main

Range	PrismaSeT
Range of product	PrismaSeT G
Product or component type	Mounting plate
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT Pack 250 duct PrismaSeT PrismaSeT G duct
Installation description	Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm Pack enclosure - width 300 mm
Installed device	FuPact: fixed ISFT160 - control: fuse carriers handle - vertical installation
Poles description	1 x 3P: fixed ISFT160 vertical installation
Number of vertical modules [50 mm]	6 module(s): ISFT160, direct in 300 mm Widefloor-standing duct 6 module(s): ISFT160, direct in 300 mm Widewall-mounted duct 9 module(s): ISFT160, direct in 300 mm WidePack enclosure
Standards	IEC 61439-2
Product certifications	ASTA

Complementary

Material	Sheet steel
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface finish	Textured Matt
Colour	White (RAL 9003)
Width	300 mm
Height	150 mm
Net weight	0.4 kg
Functional unit	300 mm PrismaSeT G floor-standing duct FuPact ISFT160 fixed fuse carriers handle vertical 3P 1 direct 6 150 mm 300 mm PrismaSeT G wall-mounted duct FuPact ISFT160 fixed fuse carriers handle vertical 3P 1 direct 6 150 mm 300 mm Prisma Pack 250 Pack enclosure FuPact ISFT160 fixed fuse carriers handle vertical 3P 1 direct 9 150 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.200 cm
Package 1 Width	9.100 cm
Package 1 Length	22.000 cm
Package 1 Weight	390.000 g
Unit Type of Package 2	CAR
Number of Units in Package 2	12
Package 2 Height	21.000 cm
Package 2 Width	38.500 cm

Package 2 Length	58.500 cm
Package 2 Weight	5.109 kg
Unit Type of Package 3	P06
Number of Units in Package 3	12
Package 3 Height	35.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	11.000 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations