

# LVS03261

Modular front plate, PrismaSeT G, Cut-out type, for ComPact NG160/modular device 3P/4P, 6M, enclosure W600mm



## Main

Range	PrismaSeT
Range of product	PrismaSeT G
Product or component type	Incoming functional unit
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT Pack 250 enclosure
Type of front plate	Cut-out
Installed device	Acti 9: fixed modular device Multi9: fixed modular device ComPact: fixed NG160 without earth leakage protection - control: toggle ComPact: fixed NG160 with earth leakage protection - control: toggle
Poles description	1 x 3P: modular rail support: NG160 1 x 4P: modular rail support: NG160
Operating position	Vertical

## Complementary

Enclosure/cubicle description	Pack enclosure - width 600 mm
Number of horizontal rows	1
Number of vertical modules [50 mm]	6
Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASTA
Surface finish	Matt Textured
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9003)
Height	300 mm
Width	600 mm
Net weight	1.84 kg
Quantity per set	Set of 1
Functional unit	600 mm Prisma Pack 250 Pack enclosure Acti 9 modular device fixed 48 direct 6 125 mm 600 mm Prisma Pack 250 Pack enclosure Multi9 modular device fixed 48 direct 6 125 mm 600 mm Prisma Pack 250 Pack enclosure ComPact NG160 without fixed toggle 3P 1 direct 6 125 mm 600 mm Prisma Pack 250 Pack enclosure ComPact NG160 without fixed toggle 4P 1 direct 6 125 mm 600 mm Prisma Pack 250 Pack enclosure ComPact NG160 with fixed toggle 3P 1 direct 6 125 mm 600 mm Prisma Pack 250 Pack enclosure ComPact NG160 with fixed toggle 4P 1 direct 6 125 mm

## Environment

IP degree of protection	IP30
-------------------------	------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.5 cm
Package 1 Width	51.0 cm
Package 1 Length	69.0 cm
Package 1 Weight	2.334 kg
Unit Type of Package 2	P12
Number of Units in Package 2	30
Package 2 Height	113.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	81.5 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
PVC free	Yes
Halogen content performance	Halogen free plastic parts product