



Main

Range	PrismaSeT
Range of product	PrismaSeT G PrismaSeT P
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT G enclosure PrismaSeT PrismaSeT P cubicle
Type of front plate	Cut-out
Installed device	ComPact: fixed INS320...400 - control: direct front rotary handle - vertical installation ComPact: fixed INS500...630 - control: direct front rotary handle - vertical installation ComPact: fixed INV320...400 - control: direct front rotary handle - vertical installation ComPact: fixed INV500...630 - control: direct front rotary handle - vertical installation
Poles description	1 x 3P: mounting plate support: INS320...400 vertical installation 1 x 4P: mounting plate support: INS320...400 vertical installation 1 x 3P: mounting plate support: INS500...630 vertical installation 1 x 4P: mounting plate support: INS500...630 vertical installation 1 x 3P: mounting plate support: INV320...400 vertical installation 1 x 4P: mounting plate support: INV320...400 vertical installation 1 x 3P: mounting plate support: INV500...630 vertical installation 1 x 4P: mounting plate support: INV500...630 vertical installation
Operating position	Vertical

Complementary

Enclosure/cubicle description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Cubicle - width 650 mm depth 400 mm
Connection position	Direct connection Linergy FC
Number of vertical modules [50 mm]	10
Standards	IEC 61439-1 IEC 61439-2
Product certifications	ASTA
Material	Steel
Surface finish	Textured Matt
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9003)
Height	500 mm
Width	500 mm
Net weight	1.9 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Quantity per set	Set of 1
Functional unit	650 mm 400 mm PrismaSeT P cubicle ComPact INS320...400 fixed direct front rotary handle vertical 3P 1 direct 10 650 mm 400 mm PrismaSeT P cubicle ComPact INS320...400 fixed direct front rotary handle vertical 4P 1 direct 10 650 mm 400 mm PrismaSeT P cubicle ComPact INS500...630 fixed direct front rotary handle vertical 3P 1 direct 11 650 mm 400 mm PrismaSeT P cubicle ComPact INS500...630 fixed direct front rotary handle vertical 4P 1 direct 11 650 mm 400 mm PrismaSeT P cubicle ComPact INV320...400 fixed direct front rotary handle vertical 3P 1 direct 10 650 mm 400 mm PrismaSeT P cubicle ComPact INV320...400 fixed direct front rotary handle vertical 4P 1 direct 10 650 mm 400 mm PrismaSeT P cubicle ComPact INV500...630 fixed direct front rotary handle vertical 3P 1 direct 11 650 mm 400 mm PrismaSeT P cubicle ComPact INV500...630 fixed direct front rotary handle vertical 4P 1 direct 11 600 mm PrismaSeT G floor-standing enclosure ComPact INS320...400 fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 10 600 mm PrismaSeT G wall-mounted enclosure ComPact INS320...400 fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 10 600 mm PrismaSeT G floor-standing enclosure ComPact INS320...400 fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 10 600 mm PrismaSeT G wall-mounted enclosure ComPact INS320...400 fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 10 600 mm PrismaSeT G floor-standing enclosure ComPact INS500...630 fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 12 600 mm PrismaSeT G wall-mounted enclosure ComPact INS500...630 fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 12 600 mm PrismaSeT G floor-standing enclosure ComPact INS500...630 fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 12 600 mm PrismaSeT G wall-mounted enclosure ComPact INS500...630 fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 12 600 mm PrismaSeT G floor-standing enclosure ComPact INV320...400 fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 10 600 mm PrismaSeT G wall-mounted enclosure ComPact INV320...400 fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 10 600 mm PrismaSeT G floor-standing enclosure ComPact INV320...400 fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 10 600 mm PrismaSeT G wall-mounted enclosure ComPact INV320...400 fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 10 600 mm PrismaSeT G floor-standing enclosure ComPact INV500...630 fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 12 600 mm PrismaSeT G wall-mounted enclosure ComPact INV500...630 fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 12 600 mm PrismaSeT G floor-standing enclosure ComPact INV500...630 fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 12 600 mm PrismaSeT G wall-mounted enclosure ComPact INV500...630 fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 12

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	51.2 cm
Package 1 Length	51.2 cm
Package 1 Weight	1.881 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	6
Package 2 Height	11.0 cm
Package 2 Width	52.5 cm
Package 2 Length	52.5 cm
Package 2 Weight	11.733 kg
Unit Type of Package 3	P12
Number of Units in Package 3	72
Package 3 Height	76.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	152.0 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
PVC free	Yes
Halogen content performance	Halogen free plastic parts product