

LVS03428

Mounting Plate, PrismaSeT P, NSX/INS/INV
250A 3P/4P rotary source changeover vertical
fixed, enclosure W650



Main

Range	PrismaSeT
Range of product	PrismaSeT P
Product or component type	Mounting plate
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT P cubicle
Installation description	Cubicle - width 650 mm depth 400 mm
Installed device	ComPact: fixed INS250 source changeover - control: direct front rotary handle - vertical installation ComPact: fixed INS250 source changeover - control: mechanical interlock - vertical installation ComPact: fixed INV250 source changeover - control: mechanical interlock - vertical installation Source changeover: fixed NSX100...250 source changeover - control: mechanical interlock - vertical installation
Poles description	2 x 3P: fixed INS250 source changeover vertical installation 2 x 4P: fixed INS250 source changeover vertical installation 2 x 3P: fixed INV250 source changeover vertical installation 2 x 4P: fixed INV250 source changeover vertical installation 2 x 3P: fixed NSX100...250 source changeover vertical installation 2 x 4P: fixed NSX100...250 source changeover vertical installation
Number of vertical modules [50 mm]	9 module(s): INS250 source changeover, direct in 650 mm Widecubicle 9 module(s): INV250 source changeover, direct in 650 mm Widecubicle 10 module(s): NSX100...250 source changeover, direct in 650 mm Widecubicle
Standards	IEC 61439-2
Product certifications	ASTA

Complementary

Material	Sheet steel
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface finish	Matt Textured
Colour	White (RAL 9003)
Width	536 mm
Height	289 mm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Net weight	3.3 kg
Functional unit	650 mm 400 mm PrismaSeT P cubicle ComPact INS250 source changeover fixed direct front rotary handle vertical 3P 2 direct 9 112.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact INS250 source changeover fixed direct front rotary handle vertical 4P 2 direct 9 112.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact INS250 source changeover fixed mechanical interlock vertical 3P 2 direct 9 112.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact INS250 source changeover fixed mechanical interlock vertical 4P 2 direct 9 112.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact INV250 source changeover fixed mechanical interlock vertical 3P 2 direct 9 112.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact INV250 source changeover fixed mechanical interlock vertical 4P 2 direct 9 112.5 mm 650 mm 400 mm PrismaSeT P cubicle source changeover NSX100...250 source changeover fixed mechanical interlock vertical 3P 2 direct 10 112.5 mm 650 mm 400 mm PrismaSeT P cubicle source changeover NSX100...250 source changeover fixed mechanical interlock vertical 4P 2 direct 10 112.5 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.500 cm
Package 1 Width	29.000 cm
Package 1 Length	57.500 cm
Package 1 Weight	3.386 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	3
Package 2 Height	14.500 cm
Package 2 Width	39.500 cm
Package 2 Length	59.500 cm
Package 2 Weight	11.054 kg
Unit Type of Package 3	P12
Number of Units in Package 3	36
Package 3 Height	104.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	144.648 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations