


# LVS03454

Mounting plate, PrismaSeT P, for Vigi NSX/  
CVS 4P 630A, horizontal plugin toggle/rot  
handle/mot mech, W650mm





## Main

Range	PrismaSeT
Range of product	PrismaSeT P
Product or component type	Mounting plate
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT P cubicle
Installation description	Cubicle - width 650 mm depth 400 mm

Installed device	<p>EasyPact: fixed CVS400 without earth leakage protection - control: direct front rotary handle - horizontal installation</p> <p>EasyPact: fixed CVS630 without earth leakage protection - control: direct front rotary handle - horizontal installation</p> <p>ComPact: plug-in NSX400 without earth leakage protection - control: toggle - horizontal installation</p> <p>ComPact: fixed NSX400 without earth leakage protection - control: direct front rotary handle - horizontal installation</p> <p>ComPact: fixed NSX400 without earth leakage protection - control: motor mechanism - horizontal installation</p> <p>ComPact: plug-in NSX400 without earth leakage protection - control: direct front rotary handle - horizontal installation</p> <p>ComPact: plug-in NSX400 without earth leakage protection - control: motor mechanism - horizontal installation</p> <p>ComPact: plug-in NSX630 without earth leakage protection - control: toggle - horizontal installation</p> <p>ComPact: fixed NSX630 without earth leakage protection - control: direct front rotary handle - horizontal installation</p> <p>ComPact: fixed NSX630 without earth leakage protection - control: motor mechanism - horizontal installation</p> <p>ComPact: plug-in NSX630 without earth leakage protection - control: direct front rotary handle - horizontal installation</p> <p>ComPact: plug-in NSX630 without earth leakage protection - control: motor mechanism - horizontal installation</p> <p>EasyPact: fixed CVS400 with earth leakage protection - control: direct front rotary handle - horizontal installation</p> <p>EasyPact: fixed CVS630 with earth leakage protection - control: direct front rotary handle - horizontal installation</p> <p>ComPact: plug-in NSX400 with earth leakage protection - control: toggle - horizontal installation</p> <p>ComPact: fixed NSX400 with earth leakage protection - control: direct front rotary handle - horizontal installation</p> <p>ComPact: fixed NSX400 with earth leakage protection - control: motor mechanism - horizontal installation</p> <p>ComPact: plug-in NSX400 with earth leakage protection - control: direct front rotary handle - horizontal installation</p> <p>ComPact: plug-in NSX400 with earth leakage protection - control: motor mechanism - horizontal installation</p> <p>ComPact: plug-in NSX630 with earth leakage protection - control: toggle - horizontal installation</p> <p>ComPact: fixed NSX630 with earth leakage protection - control: direct front rotary handle - horizontal installation</p> <p>ComPact: fixed NSX630 with earth leakage protection - control: motor mechanism - horizontal installation</p> <p>ComPact: plug-in NSX630 with earth leakage protection - control: direct front rotary handle - horizontal installation</p> <p>ComPact: plug-in NSX630 with earth leakage protection - control: motor mechanism - horizontal installation</p>
Poles description	<p>1 x 4P: fixed CVS400 horizontal installation</p> <p>1 x 4P: fixed CVS630 horizontal installation</p> <p>1 x 4P: fixed NSX400 horizontal installation</p> <p>1 x 4P: fixed NSX630 horizontal installation</p> <p>1 x 4P: plug-in NSX400 horizontal installation</p> <p>1 x 4P: plug-in NSX630 horizontal installation</p>

Number of vertical modules [50 mm]	<p>4 module(s): NSX400 without earth leakage protection , direct in 650 mm Widecubicle</p> <p>4 module(s): NSX630 without earth leakage protection , direct in 650 mm Widecubicle</p> <p>4 module(s): NSX400 with earth leakage protection , direct in 650 mm Widecubicle</p> <p>4 module(s): NSX630 with earth leakage protection , direct in 650 mm Widecubicle</p> <p>5 module(s): CVS400 without earth leakage protection , direct in 650 mm Widecubicle</p> <p>5 module(s): CVS630 without earth leakage protection , direct in 650 mm Widecubicle</p> <p>5 module(s): NSX400 without earth leakage protection , direct in 650 mm Widecubicle</p> <p>5 module(s): NSX630 without earth leakage protection , direct in 650 mm Widecubicle</p> <p>5 module(s): CVS400 with earth leakage protection , direct in 650 mm Widecubicle</p> <p>5 module(s): CVS630 with earth leakage protection , direct in 650 mm Widecubicle</p> <p>5 module(s): NSX400 with earth leakage protection , direct in 650 mm Widecubicle</p> <p>5 module(s): NSX630 with earth leakage protection , direct in 650 mm Widecubicle</p>
Standards	IEC 61439-2
Product certifications	ASTA

### Complementary

Material	Sheet steel
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface finish	Matt Textured
Colour	White (RAL 9003)
Width	650 mm
Height	250 mm

Net weight	2.96 kg
Functional unit	650 mm 400 mm PrismaSeT P cubicle EasyPact CVS400 without fixed direct front rotary handle horizontal 4P 1 direct 5 12.5 mm 650 mm 400 mm PrismaSeT P cubicle EasyPact CVS630 without fixed direct front rotary handle horizontal 4P 1 direct 5 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX400 without plug-in toggle horizontal 4P 1 direct 4 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX400 without fixed direct front rotary handle horizontal 4P 1 direct 5 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX400 without fixed motor mechanism horizontal 4P 1 direct 5 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX400 without plug-in direct front rotary handle horizontal 4P 1 direct 5 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX400 without plug-in motor mechanism horizontal 4P 1 direct 5 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX630 without plug-in toggle horizontal 4P 1 direct 4 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX630 without fixed direct front rotary handle horizontal 4P 1 direct 5 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX630 without fixed motor mechanism horizontal 4P 1 direct 5 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX630 without plug-in direct front rotary handle horizontal 4P 1 direct 5 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX630 without plug-in motor mechanism horizontal 4P 1 direct 5 12.5 mm 650 mm 400 mm PrismaSeT P cubicle EasyPact CVS400 with fixed direct front rotary handle horizontal 4P 1 direct 5 12.5 mm 650 mm 400 mm PrismaSeT P cubicle EasyPact CVS630 with fixed direct front rotary handle horizontal 4P 1 direct 5 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX400 with plug-in toggle horizontal 4P 1 direct 4 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX400 with fixed direct front rotary handle horizontal 4P 1 direct 5 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX400 with fixed motor mechanism horizontal 4P 1 direct 5 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX400 with plug-in direct front rotary handle horizontal 4P 1 direct 5 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX400 with plug-in motor mechanism horizontal 4P 1 direct 5 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX630 with plug-in toggle horizontal 4P 1 direct 4 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX630 with fixed direct front rotary handle horizontal 4P 1 direct 5 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX630 with fixed motor mechanism horizontal 4P 1 direct 5 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX630 with plug-in direct front rotary handle horizontal 4P 1 direct 5 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX630 with plug-in motor mechanism horizontal 4P 1 direct 5 12.5 mm

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.600 cm
Package 1 Width	24.700 cm
Package 1 Length	58.000 cm
Package 1 Weight	2.994 kg
Unit Type of Package 2	S04
Number of Units in Package 2	6
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	19.760 kg
Unit Type of Package 3	P12
Number of Units in Package 3	72
Package 3 Height	103.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	235.000 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
PVC free	Yes
Halogen content performance	Halogen free plastic parts product