

LVS03462

Mounting plate, PrismaSeT P, for Vigi NSX 630A 3P/4P, horizontal withdrawable, all controls, 6M, W650mm

Main

Range	PrismaSeT
Range of product	PrismaSeT P
Product or component type	Mounting plate
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT P cubicle
Installation description	Cubicle - width 650 mm depth 400 mm
Installed device	<p>ComPact: drawout NSX400 without earth leakage protection - control: toggle - horizontal installation</p> <p>ComPact: drawout NSX400 without earth leakage protection - control: direct front rotary handle - horizontal installation</p> <p>ComPact: drawout NSX400 without earth leakage protection - control: motor mechanism - horizontal installation</p> <p>ComPact: drawout NSX630 without earth leakage protection - control: toggle - horizontal installation</p> <p>ComPact: drawout NSX630 without earth leakage protection - control: direct front rotary handle - horizontal installation</p> <p>ComPact: drawout NSX630 without earth leakage protection - control: motor mechanism - horizontal installation</p> <p>ComPact: drawout NSX400 with earth leakage protection - control: toggle - horizontal installation</p> <p>ComPact: drawout NSX400 with earth leakage protection - control: direct front rotary handle - horizontal installation</p> <p>ComPact: drawout NSX400 with earth leakage protection - control: motor mechanism - horizontal installation</p> <p>ComPact: drawout NSX630 with earth leakage protection - control: toggle - horizontal installation</p> <p>ComPact: drawout NSX630 with earth leakage protection - control: direct front rotary handle - horizontal installation</p> <p>ComPact: drawout NSX630 with earth leakage protection - control: motor mechanism - horizontal installation</p>
Poles description	<p>1 x 3P: drawout NSX400 horizontal installation</p> <p>1 x 4P: drawout NSX400 horizontal installation</p> <p>1 x 3P: drawout NSX630 horizontal installation</p> <p>1 x 4P: drawout NSX630 horizontal installation</p>
Number of vertical modules [50 mm]	<p>6 module(s): NSX400 without earth leakage protection , direct in 650 mm Widecubicle</p> <p>6 module(s): NSX630 without earth leakage protection , direct in 650 mm Widecubicle</p> <p>6 module(s): NSX400 with earth leakage protection , direct in 650 mm Widecubicle</p> <p>6 module(s): NSX630 with earth leakage protection , direct in 650 mm Widecubicle</p>
Standards	IEC 61439-2
Product certifications	ASTA

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Complementary






Material	Sheet steel
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface finish	Matt Textured
Colour	White (RAL 9003)
Width	575 mm
Height	296 mm
Net weight	3.38 kg
Functional unit	650 mm 400 mm PrismaSeT P cubicle ComPact NSX400 without drawout toggle horizontal 3P 1 direct 6 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX400 without drawout direct front rotary handle horizontal 3P 1 direct 6 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX400 without drawout motor mechanism horizontal 3P 1 direct 6 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX400 without drawout toggle horizontal 4P 1 direct 6 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX400 without drawout direct front rotary handle horizontal 4P 1 direct 6 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX400 without drawout motor mechanism horizontal 4P 1 direct 6 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX630 without drawout toggle horizontal 3P 1 direct 6 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX630 without drawout direct front rotary handle horizontal 3P 1 direct 6 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX630 without drawout motor mechanism horizontal 3P 1 direct 6 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX630 without drawout toggle horizontal 4P 1 direct 6 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX630 without drawout direct front rotary handle horizontal 4P 1 direct 6 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX630 without drawout motor mechanism horizontal 4P 1 direct 6 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX400 with drawout toggle horizontal 3P 1 direct 6 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX400 with drawout direct front rotary handle horizontal 3P 1 direct 6 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX400 with drawout motor mechanism horizontal 3P 1 direct 6 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX400 with drawout toggle horizontal 4P 1 direct 6 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX400 with drawout direct front rotary handle horizontal 4P 1 direct 6 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX400 with drawout motor mechanism horizontal 4P 1 direct 6 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX630 with drawout toggle horizontal 3P 1 direct 6 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX630 with drawout direct front rotary handle horizontal 3P 1 direct 6 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX630 with drawout motor mechanism horizontal 3P 1 direct 6 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX630 with drawout toggle horizontal 4P 1 direct 6 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX630 with drawout direct front rotary handle horizontal 4P 1 direct 6 12.5 mm 650 mm 400 mm PrismaSeT P cubicle ComPact NSX630 with drawout motor mechanism horizontal 4P 1 direct 6 12.5 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.000 cm
Package 1 Width	30.000 cm
Package 1 Length	58.000 cm
Package 1 Weight	3.477 kg
Unit Type of Package 2	S04
Number of Units in Package 2	4
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm

Package 2 Length	60.000 cm
Package 2 Weight	14.700 kg
Unit Type of Package 3	P12
Number of Units in Package 3	48
Package 3 Height	102.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	188.400 kg

Offer Sustainability

SCIP Number	4758f26b-dbf8-498a-a5c2-4de140d6aa9a
BVB	 Accepted
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
PVC free	Yes
Halogen content performance	Halogen free plastic parts product
Take-back	No