


# LVS03715

Front plate, PrismaSeT P, for ComPacT INS-INV2000 to 2500 3P/4P, 10M, vertical, fixed, white, RAL 9003



## Main

Range	PrismaSeT
Range of product	PrismaSeT P
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT P cubicle
Type of front plate	Cut-out
Installed device	ComPact: fixed INS2000...2500 - control: direct front rotary handle - vertical installation ComPact: fixed INV2000...2500 - control: direct front rotary handle - vertical installation
Poles description	1 x 3P: mounting plate support: INS2000...2500 vertical installation 1 x 4P: mounting plate support: INS2000...2500 vertical installation 1 x 3P: mounting plate support: INV2000...2500 vertical installation 1 x 4P: mounting plate support: INV2000...2500 vertical installation
Operating position	Vertical

## Complementary

Enclosure/cubicle description	Cubicle - width 650 mm depth 400 mm Cubicle - width 650 mm depth 600 mm
Connection position	Front connection Rear connection
Number of vertical modules [50 mm]	10
Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASTA
Material	Steel
Surface finish	Textured Matt
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9003)
Height	500 mm
Width	500 mm
Net weight	3.54 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Quantity per set	Set of 1
Functional unit	650 mm 400 mm PrismaSeT P cubicle ComPact INS2000...2500 fixed direct front rotary handle vertical 3P 1 front connection on adaptor 16 650 mm 400 mm PrismaSeT P cubicle ComPact INS2000...2500 fixed direct front rotary handle vertical 4P 1 front connection on adaptor 16 650 mm 600 mm PrismaSeT P cubicle ComPact INS2000...2500 fixed direct front rotary handle vertical 3P 1 rear connection on adaptor 16 650 mm 600 mm PrismaSeT P cubicle ComPact INS2000...2500 fixed direct front rotary handle vertical 4P 1 rear connection on adaptor 16 650 mm 400 mm PrismaSeT P cubicle ComPact INV2000...2500 fixed direct front rotary handle vertical 3P 1 front connection on adaptor 16 650 mm 400 mm PrismaSeT P cubicle ComPact INV2000...2500 fixed direct front rotary handle vertical 4P 1 front connection on adaptor 16 650 mm 600 mm PrismaSeT P cubicle ComPact INV2000...2500 fixed direct front rotary handle vertical 3P 1 rear connection on adaptor 16 650 mm 600 mm PrismaSeT P cubicle ComPact INV2000...2500 fixed direct front rotary handle vertical 4P 1 rear connection on adaptor 16

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.000 cm
Package 1 Width	50.000 cm
Package 1 Length	50.000 cm
Package 1 Weight	2.828 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	4
Package 2 Height	22.000 cm
Package 2 Width	54.000 cm
Package 2 Length	55.000 cm
Package 2 Weight	12.200 kg
Unit Type of Package 3	P12
Number of Units in Package 3	24
Package 3 Height	81.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	82.000 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
PVC free	Yes
Halogen content performance	Halogen free plastic parts product