


# LVS03735

Front plate, PrismaSeT P, for Fupact ISFL 160 to 1250, 36M, Vertical, Through a 2/3 cut-out front plate, 185MM BCW650 IP20



## Main

Range	PrismaSeT
Range of product	PrismaSeT P
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT P cubicle
Type of front plate	Cut-out
Installed device	FuPact: fixed ISFL160 - control: fuse carriers handle - vertical installation FuPact: fixed ISFL250...630 - control: fuse carriers handle - vertical installation
Poles description	10 x 3P: mounting plate support: ISFL160 vertical installation 5 x 3P: mounting plate support: ISFL250...630 vertical installation

## Complementary

Enclosure/cubicle description	Cubicle - width 650 mm depth 400 mm
Connection position	Rear connection
Number of vertical modules [50 mm]	24
Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASTA
Material	Steel
Surface finish	Textured Matt
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9003)
Width	570 mm
Net weight	10.06 kg
Quantity per set	Set of 1
Functional unit	650 mm 400 mm PrismaSeT P cubicle FuPact ISFL160 fixed fuse carriers handle vertical 3P 10 rear connection on busbar 24 650 mm 400 mm PrismaSeT P cubicle FuPact ISFL250...630 fixed fuse carriers handle vertical 3P 5 rear connection on busbar 24

## Environment

IP degree of protection	IP20
-------------------------	------

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.0 cm
Package 1 Width	62.0 cm
Package 1 Length	125.0 cm
Package 1 Weight	10.75 kg
Unit Type of Package 2	PAL

Number of Units in Package 2	10
Package 2 Height	104.0 cm
Package 2 Width	80.0 cm
Package 2 Length	125.0 cm
Package 2 Weight	119.0 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
PVC free	Yes