



Main

Range	PrismaSeT
Range of product	PrismaSeT G
Product or component type	Connection
Product name	PrismaSeT PrismaSeT G duct
Accessory / separate part category	Current distribution accessory
Standards	IEC 61439-2, inside enclosure IEC 61439-1, inside enclosure
Product certifications	ASTA

Complementary

Cubicle-device connection	Universal power supply block
Installation description	Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm
Installed device	ComPact: fixed INS250 - control: direct front rotary handle vertical installation ComPact: fixed INV250 - control: direct front rotary handle vertical installation EasyPact: fixed CVS100...160 without earth leakage protection - control: direct front rotary handle vertical installation EasyPact: fixed CVS250 without earth leakage protection - control: direct front rotary handle vertical installation EasyPact: fixed CVS100...160 without earth leakage protection - control: toggle vertical installation EasyPact: fixed CVS250 without earth leakage protection - control: toggle vertical installation ComPact: fixed INV100 - control: direct front rotary handle vertical installation EasyPact: fixed CVS100...160 with earth leakage protection - control: toggle vertical installation EasyPact: fixed CVS250 with earth leakage protection - control: toggle vertical installation ComPact: fixed INV200 - control: direct front rotary handle vertical installation ComPact: fixed INV160 - control: direct front rotary handle vertical installation
[I _e] rated operational current	250 A
Net weight	0.78 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.4 cm
Package 1 Width	8.9 cm
Package 1 Length	29.4 cm
Package 1 Weight	766.0 g
Unit Type of Package 2	P12
Number of Units in Package 2	48
Package 2 Height	28.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	48.5 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations