



### Main

Range	PrismaSeT
Range of product	PrismaSeT P
Product or component type	Connection transfer assembly
Product name	PrismaSeT PrismaSeT P enclosure
Accessory / separate part category	Current distribution accessory
Standards	IEC 61439-2, inside enclosure IEC 61439-1, inside enclosure
Product certifications	ASTA

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Complementary

Cubicle-device connection	Connection transfer assembly
Poles description	3P
Installation description	Cubicle - width 650 mm
Installed device	<p>EasyPact: fixed CVS400 without earth leakage protection - control: toggle horizontal installation</p> <p>EasyPact: fixed CVS630 without earth leakage protection - control: toggle horizontal installation</p> <p>ComPact: fixed NSX400 with earth leakage protection - control: toggle horizontal installation</p> <p>ComPact: fixed NSX630 with earth leakage protection - control: toggle horizontal installation</p> <p>ComPact: plug-in NSX400 without earth leakage protection - control: toggle horizontal installation</p> <p>ComPact: plug-in NSX630 without earth leakage protection - control: toggle horizontal installation</p> <p>ComPact: drawout NSX400 without earth leakage protection - control: toggle horizontal installation</p> <p>ComPact: drawout NSX630 without earth leakage protection - control: toggle horizontal installation</p> <p>ComPact: plug-in NSX400 with earth leakage protection - control: toggle horizontal installation</p> <p>ComPact: plug-in NSX630 with earth leakage protection - control: toggle horizontal installation</p> <p>ComPact: drawout NSX400 with earth leakage protection - control: toggle horizontal installation</p> <p>ComPact: drawout NSX630 with earth leakage protection - control: toggle horizontal installation</p> <p>EasyPact: fixed CVS400 without earth leakage protection - control: direct front rotary handle horizontal installation</p> <p>EasyPact: fixed CVS630 without earth leakage protection - control: direct front rotary handle horizontal installation</p> <p>ComPact: fixed NSX400 without earth leakage protection - control: direct front rotary handle horizontal installation</p> <p>ComPact: fixed NSX400 without earth leakage protection - control: motor mechanism horizontal installation</p> <p>ComPact: plug-in NSX400 without earth leakage protection - control: direct front rotary handle horizontal installation</p> <p>ComPact: plug-in NSX400 without earth leakage protection - control: motor mechanism horizontal installation</p> <p>ComPact: drawout NSX400 without earth leakage protection - control: direct front rotary handle horizontal installation</p> <p>ComPact: drawout NSX400 without earth leakage protection - control: motor mechanism horizontal installation</p> <p>ComPact: fixed NSX630 without earth leakage protection - control: direct front rotary handle horizontal installation</p> <p>ComPact: fixed NSX630 without earth leakage protection - control: motor mechanism horizontal installation</p> <p>ComPact: plug-in NSX630 without earth leakage protection - control: direct front rotary handle horizontal installation</p> <p>ComPact: plug-in NSX630 without earth leakage protection - control: motor mechanism horizontal installation</p> <p>ComPact: drawout NSX630 without earth leakage protection - control: direct front rotary handle horizontal installation</p> <p>ComPact: drawout NSX630 without earth leakage protection - control: motor mechanism horizontal installation</p> <p>EasyPact: fixed CVS400 with earth leakage protection - control: toggle horizontal installation</p> <p>EasyPact: fixed CVS400 with earth leakage protection - control: direct front rotary handle horizontal installation</p> <p>EasyPact: fixed CVS630 with earth leakage protection - control: toggle horizontal installation</p> <p>EasyPact: fixed CVS630 with earth leakage protection - control: direct front rotary handle horizontal installation</p> <p>ComPact: fixed NSX400 with earth leakage protection - control: direct front rotary handle horizontal installation</p> <p>ComPact: fixed NSX400 with earth leakage protection - control: motor mechanism horizontal installation</p> <p>ComPact: plug-in NSX400 with earth leakage protection - control: direct front rotary handle horizontal installation</p> <p>ComPact: plug-in NSX400 with earth leakage protection - control: motor mechanism horizontal installation</p> <p>ComPact: drawout NSX400 with earth leakage protection - control: direct front rotary handle horizontal installation</p> <p>ComPact: drawout NSX400 with earth leakage protection - control: motor mechanism horizontal installation</p> <p>ComPact: fixed NSX630 with earth leakage protection - control: direct front rotary handle horizontal installation</p> <p>ComPact: fixed NSX630 with earth leakage protection - control: motor mechanism horizontal installation</p> <p>ComPact: plug-in NSX630 with earth leakage protection - control: motor mechanism horizontal installation</p> <p>ComPact: plug-in NSX630 with earth leakage protection - control: direct front rotary handle horizontal installation</p>

[I <sub>e</sub> ] rated operational current	630 A
Busbar cross section	32 x 6 mm
Height	200 mm
Width	350 mm
Net weight	3.04 kg





## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	16.0 cm
Package 1 Width	27.5 cm
Package 1 Length	39.5 cm
Package 1 Weight	3.042 kg
Unit Type of Package 2	P12
Number of Units in Package 2	45
Package 2 Height	92.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	148.5 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
PVC free	Yes