



## Main

Range of product	Modicon M221
Product or component type	Serial line cartridge
Product compatibility	Modicon M221C

## Complementary

Integrated connection type	Non isolated serial link - screw terminal block for RS232 Non isolated serial link - screw terminal block for RS485
Transmission rate	1.2...115.2 kbit/s (115.2 kbit/s by default) for bus length of 15 m for RS485 1.2...115.2 kbit/s (115.2 kbit/s by default) for bus length of 3 m for RS232
Communication port protocol	Non isolated serial link: Modbus master/slave - RTU/ASCII or SoMachine-Network
Insulation	Non-insulated between lines and internal logic
Height	41 mm
Depth	15 mm
Width	35 mm
Net weight	0.015 kg

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.569 cm
Package 1 Width	4.742 cm
Package 1 Length	6.985 cm
Package 1 Weight	30.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	75
Package 2 Height	14.4 cm
Package 2 Width	29.2 cm
Package 2 Length	39.5 cm
Package 2 Weight	3.32 kg
Unit Type of Package 3	P12
Number of Units in Package 3	2400
Package 3 Height	105 cm
Package 3 Width	120 cm
Package 3 Length	80 cm
Package 3 Weight	111 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
PVC free	Yes
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>