

## Main

|                                    |                   |
|------------------------------------|-------------------|
| Product or component type          | Legend holder     |
| Accessory / separate part category | Marking accessory |

## Complementary

|                                       |   |
|---------------------------------------|---|
| Material                              | Plastic   |
| Device composition                    | Blank legend<br>Legend holder                           |
| Accessory / separate part destination | Ø 22 mm control or signalling unit<br>For standard head |
| Colour                                | Dark grey   |
| Range compatibility                   | Harmony XB5<br>Harmony XB4                              |
| Legend holder size                    | 30 x 40 mm  |
| Marking                               | Unmarked on 1 black side, 1 red side background         |
| Sale per indivisible quantity         | 10  |
| Net weight                            | 0.002 kg  |

## Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type of Package 1       | PCE       |
| Number of Units in Package 1 | 1         |
| Package 1 Height             | 0.300 cm  |
| Package 1 Width              | 3.000 cm  |
| Package 1 Length             | 4.000 cm  |
| Package 1 Weight             | 0.900 g   |
| Unit Type of Package 2       | BB1       |
| Number of Units in Package 2 | 10        |
| Package 2 Height             | 1.500 cm  |
| Package 2 Width              | 7.000 cm  |
| Package 2 Length             | 11.000 cm |
| Package 2 Weight             | 12.000 g  |
| Unit Type of Package 3       | S02       |
| Number of Units in Package 3 | 1200      |
| Package 3 Height             | 15.000 cm |
| Package 3 Width              | 30.000 cm |
| Package 3 Length             | 40.000 cm |
| Package 3 Weight             | 1.755 kg  |

## Offer Sustainability

|   |   |
|---|---|
| Packaging without single use plastic                  | No  |
| REACH Regulation                                      | <a href="#">REACH Declaration</a>   |
| REACH free of SVHC                                    | Yes   |
| EU RoHS Directive                                     | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>  |
| Toxic heavy metal free                                | Yes   |
| Mercury free  | Yes   |
| RoHS exemption information                            | <a href="#">Yes</a>   |
| China RoHS Regulation                                 | <a href="#">China RoHS Declaration</a>  |
| California proposition 65                             | "WARNING: This product can expose you to chemicals including: Diisodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> " |
| Take-back   | No  |
| Carbon footprint (kg.eq.CO2 per CR, Total Life cycle) | 1   |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|