

Product data sheet

Characteristics

10MP-WE

SWITCHED SOCKET MECHANISM P/MOUNT



Main

Range of product	Standard Series
Product or component type	Socket-outlet
Colour	White electric
Product brand	Clipsal
Quantity per set	Set of 1
Cover type	Complete housing
Socket additional information	With hinged lid

Complementary

Colour code	WE
Marking	Without marking
Local signalling	Without light indicator
Device mounting	Flush
Fixing mode	By screws
[In] rated current	10 A
[Ue] rated operational voltage	250 V AC
Depth	33 mm
Length	43 mm
Width	42 mm
Fixing center	84 mm
Number of poles	1

Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---------------------------------------------------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	47.1 g
Package 1 Height	34 mm
Package 1 width	43 mm
Package 1 Length	43 mm
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Weight	0.266 kg
Package 2 Height	70 mm
Package 2 width	88 mm
Package 2 Length	110 mm
Unit Type of Package 3	CAR

Number of Units in Package 3	50
Package 3 Weight	50 kg
Package 3 Height	117 mm
Package 3 width	250 mm
Package 3 Length	310 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile