



Main

| | |
|---------------------------|------------|
| Range | Clipsal |
| Product or component type | Floodlight |
| Device application | Lighting |

Complementary

| | |
|--------------------------------|-------------------------------|
| Type of installation | Outdoor |
| Device mounting | Surface |
| Total system power | 100 W |
| Light source | LED |
| [Ue] rated operational voltage | 240 V AC 50 Hz |
| Luminous flux | 9000 lm |
| Colour rendering index | R _a =70 |
| Bulb lifespan | 30000 h |
| Colour temperature | 4000 K |
| Beam angle | 100 ° |
| Electrical insulation class | Class I |
| Height | Body with trunion arm: 260 mm |
| Width | 357 mm |
| Depth | 45 mm |
| Net weight | 2.45 kg |
| Cable length | 0.9 m |

Environment

| | |
|---------------------------------------|--------------------------|
| IP degree of protection | IP65 |
| Ambient air temperature for operation | -10...40 °C |
| Relative humidity | 10...95 % non-condensing |

Packing Units

| | |
|------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 8.4 cm |
| Package 1 Width | 33.0 cm |
| Package 1 Length | 41.4 cm |
| Package 1 Weight | 3.278 kg |
| Unit Type of Package 2 | CAR |
| Number of Units in Package 2 | 2 |
| Package 2 Height | 17.4 cm |

| | |
|------------------|---------|
| Package 2 Width | 34.6 cm |
| Package 2 Length | 42.8 cm |
| Package 2 Weight | 7.1 kg |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation |  REACH Declaration |
| EU RoHS Directive | Compliant with Exemptions |
| China RoHS Regulation |  China RoHS Declaration |
| RoHS exemption information |  Yes |
| Environmental Disclosure |  Product Environmental Profile |
| Circularity Profile |  End Of Life Information |

Contractual warranty

| | |
|----------|---------|
| Warranty | 3-Years |
|----------|---------|