


Product data sheet

Characteristics

1208060

Thorsman - TOG - M5x80 mm - cavity fixing spring toggle - set of 50



Main

Range of product	Thorsman
Product or component type	Cavity fixing
Product name	Thorsman TOG
Device short name	TOG
Provided equipment	Screw
Mounting support	Board material
Device application	Board material
Mounting support	Wall mounted
Thread type	M5
Screw diameter	5 mm
Screw length	80 mm
Drilling diameter	14 mm
Colour tint	Metal

Complementary

Quantity per set	Set of 50
Sale per indivisible quantity	50




Environment

Material	Screw: steel electroplated Cavity fixing: sheet metal electroplated
Practical load capacity	Pull-out load: 180 N for 13 mm plasterboard
Thickness	0...45 mm fixture
Environmental characteristic	Fire resistance

Packing Units

Package 1 Weight	12.000 g
Package 1 Height	48.000 mm
Package 1 width	11.000 mm
Package 1 Length	60.000 mm

Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	 RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes

China RoHS Regulation

 [China RoHS Declaration](#)

Environmental Disclosure

 [Product Environmental Profile](#)
