

## Product data sheet

### Characteristics

# 1244/25

## ELBOW INSP GALV COND 25MM



### Main

Product brand	Clipsal
Range of product	Series 1244

### Complementary

Material	Cast iron
Surface treatment	Galvanised
Diameter	25 mm
Connector type	Thread connector
Operating angle	90 °
Length	67 mm
Inner radius	12 mm

### Environment

Standards	AS 2052 AS 1721
-----------	--------------------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	124.69 g
Package 1 Height	4 cm
Package 1 width	4.5 cm
Package 1 Length	9.2 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	1.45 kg
Package 2 Height	9.6 cm
Package 2 width	16.8 cm
Package 2 Length	17.8 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	20
Package 3 Weight	3.3 kg
Package 3 Height	20 cm
Package 3 width	18 cm
Package 3 Length	22 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>