

Product data sheet

Characteristics

1259B20

Machined Brass, Clipsal - Cable Management, Steel Couplings, 20mm Brass Locknut



Main

Range	Clipsal
Product or component type	Lock nut
Accessory / separate part category	Fixing accessory
Range compatibility	Clipsal
Material	Brass

Complementary



Diameter	Thread: 20 mm External: 30 mm
Height pitch dimension	1.5 mm
Threaded length	26 mm
Thickness	4.5 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.4 cm
Package 1 Width	3 cm
Package 1 Length	2.9 cm
Package 1 Weight	10 g
Unit Type of Package 2	BB1
Number of Units in Package 2	100
Package 2 Height	6.6 cm
Package 2 Width	9.8 cm
Package 2 Length	13.2 cm
Package 2 Weight	1 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration

RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
