

## Product data sheet

### Characteristics

# 1249002

## Cavity Fixing, Thorsman, TSP-10xM5, with screw, set of 25



### Main

Range of product	Thorsman
Product or component type	Cavity fixing
Device short name	TSP
Provided equipment	Screw
Mounting support	Board material - thickness: 3...40 mm
Device application	3...40 mm board material
Mounting support	Wall mounted
Thread type	M5
Screw diameter	5 mm
Screw length	75 mm
Drilling diameter	10 mm
Colour tint	Blue/white

### Complementary

Quantity per set	Set of 25
Net weight	0.00196 kg

### Environment

Material	Screw: steel electroplated Collar: PA (polyamide) Spring: PA (polyamide)
Practical load capacity	Shear: 250 N for 13 mm board 4.5) Pull-out load: 75 N for 13 mm board 6) Shear: 400 N for 2 x 13 mm board 4.5) Pull-out load: 150 N for 2 x 13 mm board 6)
Thickness	0...37 Mm fixture 13 mm board 0...24 mm fixture 2 x 13 mm board
Environmental characteristic	Corrosion resistance
Ambient air temperature for operation	-40...80 °C
Diameter	20 mm
Length	77 mm

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.000 cm
Package 1 Width	1.000 cm
Package 1 Length	8.000 cm
Package 1 Weight	12.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	25
Package 2 Height	5.800 cm
Package 2 Width	7.800 cm
Package 2 Length	12.000 cm

Package 2 Weight	338.000 g
Unit Type of Package 3	P12
Number of Units in Package 3	42750
Package 3 Height	100.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	556.293 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

### Contractual warranty

Warranty	18 months
----------	-----------