

Product data sheet

Characteristics

1259S50

Machined Brass, Clipsal - Cable Management,
Steel Couplings, 50mm Steel Locknut



Main

Range	Clipsal
Product or component type	Lock nut
Accessory / separate part category	Fixing accessory
Range compatibility	Clipsal
Material	Steel

Complementary

Diameter	Thread: 50 mm External: 75 mm
Height pitch dimension	1.5 mm
Threaded length	65 mm
Thickness	5 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	65 mm
Package 1 Width	4 mm
Package 1 Length	65 mm
Package 1 Weight	0.06 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	20
Package 2 Height	76 mm
Package 2 Width	120 mm
Package 2 Length	160 mm
Package 2 Weight	1.3 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Height	117 mm
Package 3 Width	250 mm
Package 3 Length	310 mm
Package 3 Weight	6.5 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations