

Product data sheet

Characteristics

1511203

Thorsman installation material, shield anchor, M8 x 55mm, set of 100



Main

Range of product	Thorsman
Product or component type	Anchor
Mounting support	Brick Rock Concrete Stone
Drilling diameter	14 mm
Minimum drilling depth	60 mm
Thread type	M8
Threaded length	55 mm
Practical load capacity	4 kN pull-out load concrete
Material	Steel

Complementary

Surface finish	Zinc plated
----------------	-------------

Environment

Quantity per set	Set of 100
Sale per indivisible quantity	100

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.3 cm
Package 1 Width	1.3 cm
Package 1 Length	5 cm
Package 1 Weight	24 g
Unit Type of Package 2	BB1
Number of Units in Package 2	100
Package 2 Height	8 cm
Package 2 Width	10.1 cm
Package 2 Length	18 cm
Package 2 Weight	2.4 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	600
Package 3 Height	16 cm
Package 3 Width	23 cm
Package 3 Length	30 cm
Package 3 Weight	14.61 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------