

Product data sheet

Characteristics

1511203

Thorsman - shield anchor - M8 x 55mm - set of 100



Main

Range of product	Thorsman
Product or component type	Anchor
Mounting support	Brick Rock Concrete Stone
Drilling diameter	14 mm
Minimum drilling depth	60 mm
Thread type	M8
Threaded length	55 mm
Practical load capacity	4 kN pull-out load concrete
Material	Steel

Complementary

Surface finish	Zinc plated
----------------	-------------

Environment

Quantity per set	Set of 100
Sale per indivisible quantity	100

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	24.0 g
Package 1 Height	1.3 cm
Package 1 width	1.3 cm
Package 1 Length	5.0 cm

Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------