

Product data sheet

Characteristics

15337

IH mechanical time switch, Acti9, 24 h, 150 h memory



Main

Range of product	Acti9
Product name	Acti9 IH
Device short name	IH
Product or component type	Mechanical time switch
Number of channels	2
Function available	Manual time changeover

Complementary

Device application	Building
Load type	Parallel-corrected fluorescent tube 1 x conventional ballast 58 W Non-corrected fluorescent tube 10 x conventional ballast 58 W Serial-corrected fluorescent tube 10 x conventional ballast 58 W Non-corrected fluorescent tube 15 x conventional ballast 40 W Serial-corrected fluorescent tube 15 x conventional ballast 40 W Parallel-corrected fluorescent tube 2 x conventional ballast 40 W 230 V AC halogen lamp 1100 W 230 V AC incandescent lamp 1100 W Dual mounted fluorescent tube 3 x conventional ballast 2 x 100 W Dual mounted fluorescent tube 5 x conventional ballast 2 x 58 W Non-corrected fluorescent tube 6 x conventional ballast 100 W Serial-corrected fluorescent tube 6 x conventional ballast 100 W
Cycle duration	24 h
Maximum number of switchings	24 on - 24 off
Minimum interval duration	30 min
Type of setting	Manual time changeover
Measurement accuracy	+/- 1 s/day 20 °C
Power consumption in VA	2.5 VA
Maximum switching current	16 A - 250 V AC pf = 1 4 A - 250 V AC pf = 0.6
[Ue] rated operational voltage	230 V AC - 15...10 % at 50/60 Hz
Battery life	6 year(s)
Backup time	150 h time and program saving
Mounting support	DIN rail
9 mm pitches	6
Colour tint	White (RAL 9003)
Connections - terminals	Screw terminals
Width	54 mm
Height	82 mm
Depth	66 mm
Net weight	0.216 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Ambient air temperature for operation	-20...55 °C
IP degree of protection	Terminals: IP20 B

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.8 cm
Package 1 Width	7.8 cm
Package 1 Length	10.8 cm
Package 1 Weight	230 g

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------