

## Product data sheet

### Characteristics

# 15331

## Acti9 - IHH - mechanical time switch - 7 days - 150 h memory



### Main

Range of product	Acti 9
Product name	Acti 9 IHH
Device short name	IHH
Product or component type	Mechanical time switch
Number of channels	1
Function available	Manual time changeover

### Complementary

Device application	Building
Load type	Parallel-corrected fluorescent tube 5 x 58 W 4.7 µF Parallel-corrected fluorescent tube 7 x 40 W 7 µF Parallel-corrected fluorescent tube 2 x 100 W 18 µF 230 V AC halogen lamp 1000 W 230 V AC incandescent lamp 1000 W Fluocompact lamp 700 VA Compact fluorescent lamp 150 W LED lamp < 2 W 30 W LED lamp > 2 W 300 W
Cycle duration	7 days
Maximum number of switchings	42 on - 42 off
Minimum interval duration	2 h
Type of setting	Manual time changeover
Measurement accuracy	+/- 1 s/day 20 °C
Power consumption in W	0.5 W
Maximum switching current	16 A - 250 V AC pf = 1 4 A - 250 V AC pf = 0.6
[Ue] rated operational voltage	230...240 V AC at 50...60 Hz
Battery life	10 year(s)
Backup time	150 h time and program saving
Mounting support	DIN rail
9 mm pitches	2
Colour tint	White (RAL 9003)
Connections - terminals	Screw terminals
Width	18 mm
Height	90 mm
Depth	66 mm
Product weight	0.101 kg

### Environment

Ambient air temperature for operation	-10...50 °C
IP degree of protection	Terminals: IP20 B

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	99 g
Package 1 Height	7 cm
Package 1 width	7 cm
Package 1 Length	10 cm
Unit Type of Package 2	S03
Number of Units in Package 2	150
Package 2 Weight	15.572 kg
Package 2 Height	30 cm
Package 2 width	30 cm
Package 2 Length	40 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>

## Contractual warranty

Warranty	18 months
----------	-----------