

Product data sheet

Characteristics

2031D32N-WE

SWITCH COOK.D/POLE 32A NEON



Main

Range of product	Series 2000
Product brand	Clipsal
Device presentation	Basic element with full cover plate

Complementary

Switch function	2-pole
Number of rocker	1
Number of poles	2
Device mounting	Flush
Fixing mode	By screws
Local signalling	neon
[Ue] rated operational voltage	415 V AC
Rated current	32 A
Marking	Without marking
Actuator	Rocker

Environment

Standards	AS/NZS 3133
-----------	-------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.124 kg
Package 1 Height	28 mm
Package 1 width	76 mm
Package 1 Length	117 mm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	1.37 kg
Package 2 Height	126 mm
Package 2 width	160 mm
Package 2 Length	162 mm
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Weight	50 kg
Package 3 Height	254 mm

Package 3 width	348 mm
Package 3 Length	445 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile