

Product data sheet

Characteristics

15335

Acti9, IH, mechanical time switch, 24 h, without memory



Main

Range of product	Acti9
Product name	Acti9 IH
Device short name	IH
Product or component type	Mechanical time switch
Number of channels	1
Function available	Manual time changeover

Complementary

Device application	Building
Load type	Parallel-corrected fluorescent tube 5 x 58 W 4.7 µF Parallel-corrected fluorescent tube 7 x 40 W 7 µF Parallel-corrected fluorescent tube 2 x 100 W 18 µF 230 V AC halogen lamp 1000 W 230 V AC incandescent lamp 1000 W Fluocompact lamp 700 VA Compact fluorescent lamp 150 W LED lamp < 2 W 30 W LED lamp > 2 W 300 W
Cycle duration	24 h
Maximum number of switchings	48 on - 48 off
Minimum interval duration	15 min
Type of setting	Manual time changeover
Measurement accuracy	+/- 1 s/day 20 °C
Power consumption in W	0.5 W
Maximum switching current	16 A - 250 V AC pf = 1 4 A - 250 V AC pf = 0.6
[Ue] rated operational voltage	230 V AC at 50 Hz
Mounting support	DIN rail
9 mm pitches	2
Colour tint	White (RAL 9003)
Connections - terminals	Screw terminals
Width	18 mm
Height	90 mm
Depth	66 mm
Net weight	0.097 kg

Environment

Ambient air temperature for operation	-25...50 °C
IP degree of protection	Terminals: IP20 B

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.100 cm
Package 1 Width	7.100 cm
Package 1 Length	9.900 cm
Package 1 Weight	82.0 g
Unit Type of Package 2	S03
Number of Units in Package 2	100
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	8.695 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------