

Product data sheet

Characteristics

2031D32N-WE

2000 Series, Electric Range Switches 415V
32A Double Pole - with Neon



Main

Range of product	Series 2000
Product brand	Clipsal
Device presentation	Basic element with full cover plate

Complementary

Switch function	2-pole
Number of rocker	1
Number of poles	2
Device mounting	Flush
Fixing mode	By screws
Local signalling	neon
[Ue] rated operational voltage	415 V AC
Rated current	32 A
Marking	Without marking
Actuator	Rocker

Environment

Standards	AS/NZS 3133
-----------	-------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	28 mm
Package 1 Width	76 mm
Package 1 Length	117 mm
Package 1 Weight	0.124 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	12.6 cm
Package 2 Width	16.0 cm
Package 2 Length	16.2 cm
Package 2 Weight	1.37 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Height	25.4 cm

Package 3 Width	34.8 cm
Package 3 Length	44.5 cm
Package 3 Weight	50.0 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations