

## Product data sheet

### Characteristics

# 2031VA-WE

2000 Series, Flush Switch 1 Gang, 250VAC,  
10A, Standard, Vertical



### Main

Range of product	Series 2000
Product brand	Clipsal
Device presentation	Basic element with full cover plate and grid

### Complementary

Switch function	1-pole
Number of rocker	1
Number of poles	1
Device mounting	Flush
Fixing mode	By screws
Material	PC (polycarbonate)
Surface finish	Glossy
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A 8 AX, fluorescent lamp
Marking	Without marking
Actuator	Rocker

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.8 cm
Package 1 Width	7 cm
Package 1 Length	11.4 cm
Package 1 Weight	67 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	12.6 cm
Package 2 Width	15 cm
Package 2 Length	16.4 cm
Package 2 Weight	732 g
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Height	27 cm
Package 3 Width	35.4 cm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Package 3 Length	45.1 cm
Package 3 Weight	7.888 kg

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations