

Product data sheet

Characteristics

230DRAQ

Resimax Meterbox 21 module - H680 x W470 x D280 mm



Main

Range of product	Resi MAX
Product type	Meter box
Enclosure type	Plain door enclosure
Device application	Metering Distribution
Targeted country	Queensland

Complementary

Enclosure mounting	Semi flush Surface
Number of modules	21
Provided equipment	Enclosure Earth and neutral grid assembly Removable meter panel Fascia plate DIN rail
Function available	Cable protection slide
Protection device type	Miniature circuit breaker (MCB) - 63 A - 2P - 6 kA
Cable entry	Knock-out top and bottom Knock-out rear
Type of door	Ventilated removable door with door retainer
Door opening side	Right
Lock type	Padlockable
Material	Iron (galvanised)
Surface finish	Epoxy powder coat
Width	470 mm
Height	680 mm
Depth	280 mm

Environment


IP degree of protection	IP23
Standards	AS/NZS 3000

Packing Units

Package 1 Weight	17000.000 g
Package 1 Height	295.000 mm
Package 1 width	695.000 mm
Package 1 Length	485.000 mm

Offer Sustainability

EU RoHS Directive

Pro-active compliance (Product out of EU RoHS legal scope)  [EU RoHS Declaration](#)