

## Product data sheet

### Characteristics

## 16L-WE

### Modena/Strato, Single Switched Socket Skirting Mount Lighting



#### Main

Range of product	Standard Series
Product or component type	Switched socket
Product brand	Clipsal

#### Complementary

Control type	ON/OFF button
Number of gangs	1 gang
Pin number	3
Number Of Outlets	1
Actuator	Switch Rocker
Mounting Type	By screws
Local signalling	Without light indicator
Installation Orientation	Horizontal
Material	Plastic
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	14 mm
Length	98 mm
Width	45 mm
Mounting Centers	78 mm

#### Environment


Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.4 cm
Package 1 Width	4.5 cm
Package 1 Length	9.8 cm
Package 1 Weight	0.116 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	5

Package 2 Height	7 cm
Package 2 Width	9.2 cm
Package 2 Length	11.8 cm
Package 2 Weight	5 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Height	25 cm
Package 3 Width	21.4 cm
Package 3 Length	33.8 cm
Package 3 Weight	100 kg

## Offer Sustainability

REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations