

Product data sheet

Characteristics

2031VA-WE

SWITCH 1 GANG VERTICAL 10A 250V



Main

Range of product	Series 2000
Product brand	Clipsal
Device presentation	Basic element with full cover plate and grid

Complementary

Switch function	1-pole
Number of rocker	1
Number of poles	1
Device mounting	Flush
Fixing mode	By screws
Material	PC (polycarbonate)
Surface finish	Glossy
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A 8 AX, fluorescent lamp
Marking	Without marking
Actuator	Rocker

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	67.0 g
Package 1 Height	2.8 cm
Package 1 width	7 cm
Package 1 Length	11.4 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	0.732 kg
Package 2 Height	12.6 cm
Package 2 width	15 cm
Package 2 Length	16.4 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Weight	7.888 kg
Package 3 Height	27 cm
Package 3 width	35.4 cm
Package 3 Length	45.1 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile