

Product data sheet

Characteristics

2032H66-WE

SWITCH 2G W/P HOR IP66 2000 SE



Main

Range of product	Series 2000
Product brand	Clipsal
Device presentation	Basic element with full cover plate and grid

Complementary

Switch function	2-way 1-way
Number of rocker	2
Device mounting	Flush
Fixing mode	By screws
Material	PC (polycarbonate)
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A 10 AX, fluorescent lamp
Marking	Without marking
Actuator	Rocker

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	138.0 g
Package 1 Height	5.5 cm
Package 1 width	7.5 cm
Package 1 Length	12.5 cm
Unit Type of Package 2	CAR
Number of Units in Package 2	25
Package 2 Weight	3.6 kg
Package 2 Height	23.7 cm
Package 2 width	20.3 cm
Package 2 Length	30 cm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile