

Product data sheet

Characteristics

230DRAT

Resimax Meterbox 21 module switchboard -
H680 x W470 x D280 mm



Main

Range of product	Resi MAX
Product type	Meter box
Enclosure type	Plain door enclosure
Device application	Metering Distribution
Targeted country	Australia
Targeted region	Tasmania

Complementary

Enclosure mounting	Surface Semi flush
Number of modules	21
Provided equipment	Fascia plate DIN rail Earth and neutral grid assembly Enclosure
Function available	Cable protection slide Clips lead retainer
Protection device type	Miniature circuit breaker (MCB) - 63 A - 1P - 6 kA
Cable entry	Knock-out rear and bottom
Type of door	Ventilated removable door with door retainer
Door opening side	Right
Lock type	Padlockable
Material	Iron (galvanised)
Surface finish	Epoxy powder coat
Width	470 mm
Height	680 mm
Depth	280 mm
Colour	Beige

Environment

IP degree of protection	IP23
Standards	AS/NZS 3000

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	15 kg
Package 1 Height	68 cm
Package 1 width	47 cm
Package 1 Length	28 cm

