

Product data sheet

Characteristics

21501

Acti9, comb busbar - 1L+N - 9 mm pitch - 12 modules - 80A



Main

Range	Acti9
Product or component type	Comb busbar
Mounting mode	Horizontal
Accessory / separate part category	Connection accessory
Lines description	1L + N
Length in 18 mm modules	12

Complementary

Number of ways	12 ways N + 1 L
Poles configuration for 1 way	1 x 1P + N 1 x 2P
Connection pitch	9 mm
Connector type	Tooth
Distance between way	18 mm
Marking	N L
Insulation	Insulated
Device presentation	Cuttable
[Ie] rated operational current	80 A at 40 °C
[Ue] rated operational voltage	230 V AC Ph/N
[Ui] rated insulation voltage	440 V AC conforming to IEC 61439-1
[Uimp] rated impulse withstand voltage	6 kV
Mounting location	Top on tunnel type terminals
9 mm pitches	24
Width	216 mm
Colour	Light grey (RAL 7035)
Range compatibility	Acti 9 (Acti9 iDPN) Acti 9 (Acti9 iDPN Vigi) Acti 9 (Acti9 IDc) Multi9 (Multi9 N40 Vigi) N40 Vigi Multi9 (Multi9 N40)

Environment

Standards	EN/IEC 60439-1 IEC 60947-7
Fire resistance	960 °C (30 s) conforming to IEC 60695-2-1
Pollution degree	3 conforming to IEC 60947-7

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	3.2 cm
Package 1 Length	26.9 cm
Package 1 Weight	82 g

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------