


## Product data sheet

### Characteristics

# 221/25-EO

## Conduit Locating Flange, Clipsal - Cable Management, PVC, 25mm



### Main

Colour	Electric orange
Product brand	Clipsal
Range of product	Series 221

### Complementary

Colour code	EO
Material	Plastic
External diameter	90 mm
Height	40 mm

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.9 cm
Package 1 Width	9.1 cm
Package 1 Length	9.1 cm
Package 1 Weight	0.02 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	90 cm
Package 2 Width	172 cm
Package 2 Length	210 cm
Package 2 Weight	4.55 kg
Unit Type of Package 3	PAL
Number of Units in Package 3	3600
Package 3 Height	140 cm
Package 3 Width	114 cm
Package 3 Length	114 cm
Package 3 Weight	165.2 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations