

## Product data sheet

### Characteristics

# 25D15-WE

## Twin Switch Socket Outlet, 250V, 15A, Standard Size, 2 Pole



### Main

|                           |                 |
|---------------------------|-----------------|
| Range of product          | Standard Series |
| Product or component type | Switched socket |
| Product brand             | Clipsal         |

### Complementary

|                                |                         |
|--------------------------------|-------------------------|
| Control type                   | ON/OFF button           |
| Number of gangs                | 2 gangs                 |
| Pin number                     | 3                       |
| Number of power socket outlets | 2                       |
| Actuator                       | Rocker Switch           |
| Fixing mode                    | By screws               |
| Local signalling               | Without light indicator |
| Mounting position              | Horizontal              |
| Material                       | PC (polycarbonate)      |
| Surface finish                 | Glossy                  |
| [Ue] rated operational voltage | 250 V AC                |
| [In] rated current             | 15 A                    |
| Depth                          | 16 mm                   |
| Length                         | 115 mm                  |
| Width                          | 73 mm                   |
| Fixing center                  | 84 mm                   |

### Environment

|           |  |
|-----------|--|
| Standards | AS/NZS 3100<br>AS/NZS 3112<br>AS/NZS 3133<br>AS/NZS 3000:approval number S/1 |
|-----------|--|

### Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type of Package 1       | Db      |
| Number of Units in Package 1 | 1       |
| Package 1 Height             | 11.6 cm |
| Package 1 Width              | 12.0 cm |
| Package 1 Length             | 7.3 cm  |
| Package 1 Weight             | 142.0 g |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product                         |
| REACH Regulation           | <a href="#">REACH Declaration</a>             |
| EU RoHS Directive          | Compliant <a href="#">EU RoHS Declaration</a> |
| Mercury free               | Yes   |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>        |
| RoHS exemption information | <a href="#">Yes</a>                           |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a> |