

Product data sheet

Characteristics

230DRAQ

Resi MAX Meter Boxes, Metal Meter Box,
Switch Board, Din Rail, 21 Module, H680 x
W470 x D280 mm



Main

Range of product	Resi MAX
Product type	Meter box
Enclosure type	Plain door enclosure
Device application	Metering Distribution
Targeted country	Australia
Targeted region	Queensland

Complementary

Enclosure mounting	Semi flush Surface
Number of modules	21
Provided equipment	Enclosure Earth and neutral grid assembly Removable meter panel Fascia plate DIN rail
Function available	Cable protection slide
Protection device type	Miniature circuit breaker (MCB) - 63 A - 2P - 6 kA
Cable entry	Knock-out top and bottom Knock-out rear
Type of door	Ventilated removable door with door retainer
Door opening side	Right
Lock type	Padlockable
Material	Iron (galvanised)
Surface finish	Epoxy powder coat
Width	470 mm
Height	680 mm
Depth	280 mm
Colour	Beige

Environment

IP degree of protection	IP23
Standards	AS/NZS 3000

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	29.5 cm
Package 1 Width	69.5 cm
Package 1 Length	48.5 cm
Package 1 Weight	17000 g

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
-------------------	------------------------------------------------------------------------------------------------