

## Product data sheet

### Characteristics

# 230DRAT

## Clipsal Resi MAX Meter Box Tasmania 21 Modules padlockable



### Main

Range of product	Resi MAX
Product type	Meter box
Enclosure type	Plain door enclosure
Device application	Metering Distribution
Targeted country	Australia
Targeted region	Tasmania

### Complementary

Enclosure mounting	Surface Semi flush
Number of modules	21
Provided equipment	Fascia plate DIN rail Earth and neutral grid assembly Enclosure
Function available	Cable protection slide Clips lead retainer
Protection device type	Miniature circuit breaker (MCB) - 63 A - 1P - 6 kA
Cable entry	Knock-out rear and bottom
Type of door	Ventilated removable door with door retainer
Door opening side	Right
Lock type	Padlockable
Material	Iron (galvanised)
Surface finish	Epoxy powder coat
Width	470 mm
Height	680 mm
Depth	280 mm
Colour	Beige

### Environment

IP degree of protection	IP23
Standards	AS/NZS 3000

### Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	68.0 cm
Package 1 Width	47.0 cm
Package 1 Length	28.0 cm
Package 1 Weight	15.0 kg

