

Product data sheet

Characteristics

3025CSG

Connected Socket, Iconic, BLE default mode,
Twin horizontal, 10 A, 240 V, Grid



Main

Range compatibility	Wiser mounting bracket
Product brand	Clipsal
Range	Iconic
Product or component type	Connected switched socket
Outlet poles configuration	2P + E

Complementary

Device presentation	Mechanism with fixing frame
Device mounting	Flush
Socket-outlet type	Twin switched socket-outlet
Socket number	2
Outlet standard	Australian
Rated current	10 A
[Ue] rated operational voltage	240 V AC 50 Hz
Colour tint	White
Surface finish	Matt
Local signalling	LED
Control type	Rocker on/off switching By mobile application
Software name	Wiser by SE App
Communication network type	Wireless Zigbee (2405...2480 MHz), 10 mW at < 50 m
Memory description	Backup memory - date and time for 6 h Backup memory - program for indefinite period
Material	Plastic
Type of installation	Indoor installation

Environment

IP degree of protection	IP20
Relative humidity	5...90 % non-condensing
Standards	AS/NZS 3112 safety AS/NZS 60669.2.1 safety AS/NZS 60669.2.1 EMC AS/NZS 4268 radio

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.4 cm
Package 1 Width	9.5 cm
Package 1 Length	14.1 cm
Package 1 Weight	202.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information