

## Product data sheet

### Characteristics

# 3025XA-VW

## Double Switch Power Point, Clipsal Iconic, Horizontal Mount, 250 V 10A, Extra Removable Switch

### Main

Range	Clipsal Iconic
Product or component type	Switched socket
Device presentation	Complete product
Outlet poles configuration	2P + E with shutter
Outlet standard	Australian

### Complementary

Device mounting	Flush
Number of power socket outlets	2
Number of rocker	3
Range compatibility	Clipsal Iconic
Outlet standard description	With earthing contact
Outlet standard deviation	Australian/New Zealand
Ground lug position	Straight 180° position
Fixing mode	By screw
Installation direction	Horizontal
Surface finish	Matt
Type of packing	Polybag
Quantity per set	Set of 10
Sale per indivisible quantity	1
Rated current	10 A at 230/240 V AC 50 Hz
Electrical durability	12000 cycles
Screwdriver shape	Square drive no 1 (SQ1) Philips No 2
Clamping connection capacity	1 x 2.5...4 x 2.5 mm <sup>2</sup> for stranded cable(s) 1 x 2.5...4 x 2.5 mm <sup>2</sup> for flexible cable(s) 1 x 2.5...4 x 2.5 mm <sup>2</sup> for rigid cable(s)
Wire stripping length	16 mm
Material	PC (polycarbonate): cover frame ABS (acrylonitrile butadiene-styrene): cover frame PC (polycarbonate): fixing frame PP (polypropylene): rocker POM (polyoxymethylene): shutter POM (polyoxymethylene): locking bar
Height	78 mm
Width	120 mm
Depth	37 mm
Net weight	0.092 kg
[Ue] rated operational voltage	230/240 V

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Environment

Ambient air temperature for storage	0...60 °C
Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %
Standards	AS/NZS 3112 AS/NZS 3133 AS/NZS 60669.1
Product certifications	RCM

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.4 cm
Package 1 Width	8.7 cm
Package 1 Length	14.4 cm
Package 1 Weight	132 g

## Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	Yes
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
Take-back	No
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	11