

Product data sheet

Characteristics

25DN-WE

Standard Series, Switched Socket Twin Double Pole 10A Neon



Main

Range of product	Standard Series
Product or component type	Switched socket
Product brand	Clipsal

Complementary

Control type	ON/OFF button
Number of gangs	2 gangs
Pin number	3
Number Of Outlets	2
Actuator	Rocker Switch
Mounting Type	By screws
Local signalling	Indicator light
Installation Orientation	Horizontal
Material	PC (polycarbonate)
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	16 mm
Length	115 mm
Width	73 mm
Mounting Centers	84 mm

Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133 AS/NZS 3000:approval number S/1
-----------	--

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.6 cm
Package 1 Width	7.3 cm
Package 1 Length	11.5 cm
Package 1 Weight	152.25 g

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations