

## Product data sheet

### Characteristics

# 3025XAG

Double Switch Power Point Grid with 1 extra switch, Clipsal Iconic, Horizontal Mount, 250V, 10A

#### Main

Range	Clipsal Iconic
Product or component type	Switched socket
Device presentation	Mechanism with fixing frame
Outlet poles configuration	2P + E with shutter
Outlet standard	Australian

#### Complementary

Device mounting	Flush
Number of power socket outlets	2
Number of rocker	2
Range compatibility	Clipsal Iconic cover frame
Outlet standard description	With earthing contact
Outlet standard deviation	Australian/New Zealand
Ground lug position	Straight 180° position
Number of gangs	1 gang
Fixing mode	By screw
Installation direction	Horizontal
Surface finish	Matt
Type of packing	Polybag
Quantity per set	Set of 10
Sale per indivisible quantity	1
Rated current	10 A at 230/240 V AC 50 Hz
Electrical durability	12000 cycles
Screwdriver shape	Square drive no 1 (SQ1) Philips No 2
Clamping connection capacity	1 x 2.5...4 x 2.5 mm <sup>2</sup> for stranded cable(s) 1 x 2.5...4 x 2.5 mm <sup>2</sup> for flexible cable(s) 1 x 2.5...4 x 2.5 mm <sup>2</sup> for rigid cable(s)
Wire stripping length	16 mm
Material	PC (polycarbonate): fixing frame PP (polypropylene): rocker POM (polyoxymethylene): shutter
Height	71 mm
Width	115 mm
Depth	36 mm
Net weight	0.071 kg
[Ue] rated operational voltage	230/240 V

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Environment

Ambient air temperature for storage	0...60 °C
Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %
Standards	AS/NZS 3112 AS/NZS 60669.1 AS/NZS 3133
Product certifications	RCM

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	7 cm
Package 1 Length	16 cm
Package 1 Weight	108 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	150 cm
Package 2 Width	102 cm
Package 2 Length	328 cm
Package 2 Weight	1.19 kg

## Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	Yes
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
Take-back	No
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	11