

Product data sheet

Characteristics

3043HSUSB-VW

Clipsal Iconic, 3 USB Charger, Type A, 2.1 A, 240 V, Vivid White



Main

Range	Clipsal Iconic
Product or component type	USB charger
[Ue] rated operational voltage	220/240 V AC 50 Hz
Integrated connection type	3 USB 2.0 type A 5 V DC, maximum load current: 2.1 A
Maximum load current with 2 outputs used simultaneously	4.5 A

Complementary

Device mounting	Flush
Device presentation	Complete product
Colour tint	Vivid white (VW)
Surface finish	Matt Textured
Fixing mode	By screws
Type of packing	Polybag
Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	-5...50 °C
Relative humidity	15...95 %
Protection type	Short time short-circuit protection
Number of terminals	3 screw terminal
Screwdriver shape	Square drive no 1 (SQ1) Phillips No 2
Clamping connection capacity	4 x 2.5 mm ² for stranded cable(s) 4 x 2.5 mm ² for flexible cable(s) 4 x 2.5 mm ² for rigid cable(s)
Wire stripping length	16 mm
Height	78 mm
Width	120 mm
Depth	70 mm
Embedding depth	35 mm

Environment

Product certifications	RCM
Electrical insulation class	Class II
IK degree of protection	IK04
IP degree of protection	IP21

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	167 g
Package 1 Height	55 mm
Package 1 width	98 mm
Package 1 Length	151 mm

Offer Sustainability

EU RoHS Directive	Under investigation
Environmental Disclosure	Product Environmental Profile