

Product data sheet

Characteristics

3043HSUSB-VW

Clipsal Iconic, 3 USB Charger, Type A, 2.1 A, 240 V, Vivid White



Main

Range	Clipsal Iconic
Product or component type	USB charger
[Ue] rated operational voltage	220/240 V AC 50 Hz
Integrated connection type	3 USB 2.0 type A 5 V DC, maximum load current: 2.1 A
Maximum load current with 2 outputs used simultaneously	4.5 A

Complementary

Device mounting	Flush
Device presentation	Complete product
Colour tint	Vivid white (VW)
Surface finish	Matt Textured
Fixing mode	By screws
Type of packing	Polybag
Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	-5...50 °C
Relative humidity	15...95 %
Protection type	Short time short-circuit protection
Number of terminals	3 screw terminal
Screwdriver shape	Square drive no 1 (SQ1) Philips No 2
Clamping connection capacity	4 x 2.5 mm ² for stranded cable(s) 4 x 2.5 mm ² for flexible cable(s) 4 x 2.5 mm ² for rigid cable(s)
Wire stripping length	16 mm
Height	78 mm
Width	70 mm
Depth	70 mm
Embedding depth	35 mm

Environment

Product certifications	RCM
Electrical insulation class	Class II
IK degree of protection	IK04
IP degree of protection	IP21

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	167.0 g
Package 1 Height	5.5 cm
Package 1 width	9.8 cm
Package 1 Length	15.1 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile