

## Product data sheet

### Characteristics

# 25XS-WE

## SWITCHED SOCKET TWIN 10A EXTRA SWITCH SHUTTER



### Main

|                  |                 |
|------------------|-----------------|
| Colour           | White electric  |
| Product brand    | Clipsal         |
| Range of product | Standard Series |

### Complementary

|                                |                         |
|--------------------------------|-------------------------|
| Colour code                    | WE                      |
| Control type                   | ON/OFF button           |
| Number of gangs                | 2 gangs                 |
| Pin number                     | 3                       |
| Number of power socket outlets | 2                       |
| Actuator                       | Rocker Switch           |
| Mounting position              | Horizontal              |
| Fixing mode                    | By screws               |
| Local signalling               | Without light indicator |
| Material                       | PC (polycarbonate)      |
| Surface finish                 | Glossy                  |
| [Ue] rated operational voltage | 250 V AC                |
| [In] rated current             | 10 A                    |
| Depth                          | 16 mm                   |
| Length                         | 115 mm                  |
| Width                          | 73 mm                   |
| Fixing center                  | 84 mm                   |

### Environment

|           |                                                                              |
|-----------|------------------------------------------------------------------------------|
| Standards | AS/NZS 3100<br>AS/NZS 3112<br>AS/NZS 3133<br>AS/NZS 3000:approval number S/1 |
|-----------|------------------------------------------------------------------------------|

### Packing Units

|                  |          |
|------------------|----------|
| Package 1 Weight | 0.112 kg |
|------------------|----------|

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

|                            |                                               |
|----------------------------|-----------------------------------------------|
| Sustainable offer status   | Green Premium product                         |
| REACH Regulation           | <a href="#">REACH Declaration</a>             |
| EU RoHS Directive          | Compliant <a href="#">EU RoHS Declaration</a> |
| Mercury free               | Yes                                           |
| RoHS exemption information | <a href="#">Yes</a>                           |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>        |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a> |