

Product data sheet

Characteristics

30MD-RD

Clipsal - Mechanisms, Switch Mechanisms, 30 Series, 250V 10A - Double Pole, Single Throw



Main

Range of product	Standard Series Series 30
Product brand	Clipsal
Assembly Type	Basic element




Complementary

Number of poles	2
Installation Type	Flush
Number Of Switches	1
Material	PVC (polyvinyl chloride)
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A
Load type	Fluorescent lamp 10 A LEDi lamp 100 W
Marking	Without marking
Surface finish	Glossy
Actuator	Rocker
Switch function	2-pole

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.36 cm
Package 1 Width	2.36 cm
Package 1 Length	2.9 cm
Package 1 Weight	14 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations