

## Product data sheet

### Characteristics

# 30PBBP-DB

## Push Button Mechanism, Impress Series, Momentary, 230/240V, 16A

### Main

Range of product	Impress Series 30
Product or component type	Push-button
Colour	Dark blue
Product brand	Clipsal
Device presentation	Basic element



### Complementary

Colour code	DB
Actuator	Push-button
Local signalling	Without light indicator
Material	Plastic
[Ue] rated operational voltage	250 V AC
Inrush current	16 A
Depth	10 mm
Width	21 mm
Length	21 mm
Load type	Fluorescent lamp 16 AX LEDi lamp 250 W

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.1 cm
Package 1 Width	2.3 cm
Package 1 Length	2.3 cm
Package 1 Weight	30 g

### Offer Sustainability

Packaging without single use plastic	Yes
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	 <a href="#">End Of Life Information</a>