

Product data sheet

Characteristics

3015XUAG

Clipsal Iconic, switched socket, switch & socket, 1G, horiz, 10 A



Main

| | |
|----------------------------|-----------------------------|
| Range | Clipsal Iconic |
| Product or component type | Switched socket |
| Device presentation | Mechanism with fixing frame |
| Outlet poles configuration | 2P + E with shutter |
| Outlet standard | Australian |

Complementary

| | |
|--------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Device mounting | Flush |
| Number of power socket outlets | 1 |
| Number of rocker | 1 |
| Range compatibility | Cover frame |
| Outlet standard description | With earthing contact |
| Outlet standard | Australian/New Zealand |
| Ground lug position | Straight 180° position |
| Number of gangs | 1 gang |
| Fixing mode | By screw |
| Installation direction | Horizontal |
| Colour | Ash grey |
| Surface finish | Matt |
| Type of packing | Polybag |
| Quantity per set | Set of 10 |
| Sale per indivisible quantity | 1 |
| Rated current | 10 A at 250 V AC 50 Hz |
| Electrical durability | 12000 cycles |
| Connections - terminals | 3 screw terminals |
| Screwdriver shape | Philips No 2 Square drive no 1 (SQ1) |
| Clamping connection capacity | 1 x 2.5...4 x 2.5 mm ² for rigid cable(s) 1 x 2.5...4 x 2.5 mm ² for stranded cable(s) 1 x 2.5...4 x 2.5 mm ² for flexible cable(s) |
| Wire stripping length | 16 mm |
| Material | PC (polycarbonate): fixing frame PP (polypropylene): rocker POM (polyoxymethylene): shutter POM (polyoxymethylene): locking bar |
| Height | 71 mm |
| Width | 115 mm |
| Depth | 31 mm |
| Embedding depth | 24 mm |
| Net weight | 0.082 kg |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

| | |
|---------------------------------------|-------------|
| Ambient air temperature for operation | 0...45 °C |
| Relative humidity | 10...95 % |
| Standards | AS/NZS 3112 |
| Product certifications | RCM |

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Weight | 62.45 g |
| Package 1 Height | 3.2 cm |
| Package 1 width | 6.6 cm |
| Package 1 Length | 11.6 cm |

Offer Sustainability

| | |
|----------------------------|-----------------------------------------------|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |